

K-1000-HB

Roll-Around Hangar Box For Facility Use

SPACE SAVING

VERSATILE

DURABLE

SECURITY



P.O. Box 1372 1206 E. MacArthur St. Sonoma, CA 95476 1-800-344-2393 (707) 935-1170 FAX: (707) 935-1828

CAGE Code: 64878

www.fsirivet.com

Email: sales@fsirivet.com





Introducing the new K-1000-HB Hangar Box to complement the K-1000 Sheet Metal Mechanics Tool Kit. It is designed to hold FSI's Complete K-1000 Sheet Metal Mechanics Mobility

Kit. The K-1000-HB is a perfect addition to your hangar maintenance; allowing all three mobility boxes of your K-1000 to become a Facility Kit for use on a daily basis. This new Hangar Box measures 60" x 27-3/4" x 37-1/2" high, and has five (5) full width drawers partitioned to hold two (2) trays each. The drawers are configured to house the individual K-1000 trays to make the use of all tooling easily accessible during day to day maintenance. Individual drawers have their own lock-in/lock-out latch and a hinged bar, allowing all tools to be secured with a padlock. Each Hangar Box is equipped with two (2) fixed casters and two (2) swivel casters; each with 6" polyurethane wheels and tread-locks for easy positioning at a work station or an aircraft dock. It also has a push/pull bar attached, and is complete with a 60" x 30" x 1-3/4" (thick) hardwood top.

K-1000-HB Specifications:

Total Box Weight (empty): 620 lbs.

Box Dimensions: 60" wide x 27-3/4" deep x 37-1/2" high w/ Casters attached Drawers: 55-3/8" side to side x 25-1/8" front to back

Drawer Capacity: 400 lbs. each fully extended and built on a carriage system guaranteed against failure

Drawer Stack -

#1 - Empty space on left side, plus Tray #1 of K-1000-2 on right side (2-1/4" ht)

#2 - Tray #1 of K-1000-1 on left; Tray #3 of K-1000-2 on right (2-1/4" ht)

#3 - Tray #2 of K-1000-1 on left; Tray #2 of K-1000-2 on right (4-5/8" ht)

#4 - Tray #3 of K-1000-1 on left; Tray #4 of K-1000-2 on right (5-3/8" ht)

#5 - Tray #1 of K-1000-3 on left; Tray #2 of K-1000-3 on right (5-3/8" ht)

Each K-1000-HB Hangar Box comes complete with the pre-cut foam trays that are affixed to the bottom of each of the three K-1000 Boxes: Tray #3 from K-1000-1 Box, Tray# 4 from K-1000-2 Box, and Tray #2 from K-1000-3 Box are all included. The "loose" trays from each of the K-1000 Boxes can be transferred from the Mobility Kit to their respective drawer in the K-1000-HB Hangar Box. For future deployment, the trays can be returned to the K-1000 Mobility Boxes at any time.