

3060KIT

VISU-LOK RATCHET HAND TOOL KIT

INSTRUCTIONS

1. Determine the type (Flush, Protruding, Millable) and size of the fastener being used.
2. Use the right combination of Nose and Wrench Driver.


Example:

fastener: Type Flush size 3/16" (- 6) use:


Nose: HW2002

Wrench Driver Assy: HW2001


3. Insert Wrench Driver Assy into socket and Nose and secure with Set Screw.

**ZEPHYR[®]**
T O O L
LOK-FAST

Fastener Driver	Dia.
- 5	5/32
- 6	3/16
- 8	1/4



WRENCH DRIVERS ASSY.



ZEPHYR Manufacturing Co., Inc

201 Hindry Avenue

Inglewood, CA 90301-1519

Tel. 310-410-4907 ■ Fax. 310-410-2913 ■ Email zephyr@zephyrtools.com ■ <http://www.zephyrtools.com>

Rev. 12/09